

# NS 35/ 7,5 PERF 500MM - DIN rail perforated



1207650

<https://www.phoenixcontact.com/us/products/1207650>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail perforated, acc. to EN 60715, length: 500 mm, material: Steel, galvanized, passivated with a thick layer, mounting type: Standard profile, color: silver, Current dimensional tolerances: Profile tolerance due to burr/sharp edges =  $\pm 0.5$  mm, Initial dimension =  $\pm 0.5$  mm, Hole pattern =  $\pm 0.5$  mm, Hole position =  $\pm 0.5$  mm, Minimum rail length: Unperforated:  $> 20$  mm, Perforated:  $> 100$  mm, Last punching at Phoenix Contact:  $< 1750$  mm

## Commercial data

Item number	1207650
Packing unit	1 pc
Minimum order quantity	20 pc
Sales key	BH84
Product key	BH8422
GTIN	4046356366496
Weight per piece (including packing)	162.7 g
Weight per piece (excluding packing)	155 g
Customs tariff number	72166190
Country of origin	DE

# NS 35/ 7,5 PERF 500MM - DIN rail perforated



1207650


<https://www.phoenixcontact.com/us/products/1207650>

## Technical data

### Product properties

Product type	DIN rail
--------------	----------

### Dimensions

Dimensional drawing	
Width	35 mm
Hole width	15 mm
Height	7.5 mm
Hole height	6.2 mm
Length	500 mm
Drill hole spacing	25 mm

### Material specifications

Color	silver
Material	Steel
Coating	galvanized, passivated with a thick layer

### Standards and regulations

Connection in acc. with standard	IEC / EN
Tests	acc. to EN 60715


# NS 35/ 7,5 PERF 500MM - DIN rail perforated

1207650

<https://www.phoenixcontact.com/us/products/1207650>



## Drawings



# NS 35/ 7,5 PERF 500MM - DIN rail perforated



1207650

<https://www.phoenixcontact.com/us/products/1207650>

## Classifications

### ECLASS

ECLASS-13.0

27400602

### ETIM

ETIM 9.0

EC001285

### UNSPSC

UNSPSC 21.0

39121700

# NS 35/ 7,5 PERF 500MM - DIN rail perforated



1207650

<https://www.phoenixcontact.com/us/products/1207650>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)