

# HC-M-00 - Dummy module



1414353

<https://www.phoenixcontact.com/us/products/1414353>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

HEAVYCON dummy module, for unused slots in the module carrier frame



## Commercial data

Item number	1414353
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
Catalog page	Page 594 (C-2-2019)
GTIN	4055626024660
Weight per piece (including packing)	4.58 g
Weight per piece (excluding packing)	4 g
Customs tariff number	39269097
Country of origin	PL

# HC-M-00 - Dummy module

1414353

<https://www.phoenixcontact.com/us/products/1414353>

## Technical data


### Notes

General	Connectors may be operated only when there is no load/voltage.
---------	--

### Product properties

Product type	Dummy module
Series	HC-M-00
Application	Dummy module
Number of module slots	1

### Dimensions

Dimensional drawing	
Width	34.2 mm
Height	16.8 mm
Length	14.6 mm

### Material specifications

Material	PC
Flammability rating according to UL 94	V0
Contact carrier material	PC

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

# HC-M-00 - Dummy module


1414353

<https://www.phoenixcontact.com/us/products/1414353>



## Drawings

Dimensional drawing



HC-M-00

# HC-M-00 - Dummy module



1414353

<https://www.phoenixcontact.com/us/products/1414353>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414353>

 **CSA**  
Approval ID: 13631

 **UL Recognized**  
Approval ID: E118976

# HC-M-00 - Dummy module

1414353

<https://www.phoenixcontact.com/us/products/1414353>



## Classifications

### ECLASS

ECLASS-13.0

27440192

### ETIM

ETIM 9.0

EC002943

### UNSPSC

UNSPSC 21.0

39121400

# HC-M-00 - Dummy module



1414353

<https://www.phoenixcontact.com/us/products/1414353>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.025 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)