

FOC-TOOL-SET-GOF - Tool set



1089515

<https://www.phoenixcontact.com/us/products/1089515>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Tool set for GOF assembly



Product description

Tool set for GOF assembly, for field installation of LC and SC connectors. Thanks to cleave technology, it is no longer necessary to bond and polish the connectors.

Your advantages

- Suitable for quick and easy field assembly or repair
- Cleave technology
- No bonding or polishing
- Optimum attenuation values with easy assembly
- A real alternative to splicing
- Reusable connectors

Commercial data

Item number	1089515
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNIEY
GTIN	4055626894041
Weight per piece (including packing)	1,700 g
Weight per piece (excluding packing)	1,700 g
Customs tariff number	82060000
Country of origin	BG

FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/us/products/1089515>



Set consists of

FOC-TOOL-CASE-EMPTY - FO accessories

1414095

<https://www.phoenixcontact.com/us/products/1414095>



Replacement case, empty

FOC-TOOL-FIBERCLAMP - FO accessories

1414096

<https://www.phoenixcontact.com/us/products/1414096>



Wire holder

FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/us/products/1089515>



FOC-TOOL-LIGHTSOURCE-ADAPTER - FO accessories

1414097

<https://www.phoenixcontact.com/us/products/1414097>



Red light source adapter

FOC-TOOL-LIGHTSOURCE-650 - FO accessories

1414098

<https://www.phoenixcontact.com/us/products/1414098>



Red light source (650 nm)

FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/us/products/1089515>



FOC-TOOL-STRIPPING-FA-1 - FO accessories

1414099

<https://www.phoenixcontact.com/us/products/1414099>

2-hole fiber stripper



FOC-TOOL-STRIPPING-FA-2 - FO accessories

1414100

<https://www.phoenixcontact.com/us/products/1414100>

Fiber stripper for AWG 22 - 10 / (0.6 ... 2.6 mm)



FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/us/products/1089515>



FOC-TOOL-FIBERCONTAINER - FO accessories

1414102

<https://www.phoenixcontact.com/us/products/1414102>

Fiber container



FOC-TOOL-CLEANINGWIPE - FO accessories

1414104

<https://www.phoenixcontact.com/us/products/1414104>

Fiber cleaning cloth



FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/us/products/1089515>



FOC-TOOL-MARKER BK - FO accessories

1414105

<https://www.phoenixcontact.com/us/products/1414105>



Marker pen

FOC-SC-LC-OM4-LS-CABLE/3 - FO accessories

1414106

<https://www.phoenixcontact.com/us/products/1414106>



Launch fiber multimode

FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/us/products/1089515>



FOC-SC-LC-OS2-LS-CABLE/3 - FO accessories

1414107

<https://www.phoenixcontact.com/us/products/1414107>

Launch fiber single mode (OS2)



FOC-TOOL-STRIPPING-MARKER - Distribution block

1218483

<https://www.phoenixcontact.com/us/products/1218483>

Marker for stripping FO cables



FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/us/products/1089515>



CUTFOX-ES - Cutting tool

1212621

<https://www.phoenixcontact.com/us/products/1212621>




Electrician's scissors, high cutting performance thanks to micro-serrated cutting area, suitable for copper, aluminum, Kevlar fibers, and plastic, two-component non-slip soft-grip handles, ergonomic design, adjustable screw joint

FOC-TOOL-CLEAVER-HOLDER-UNIVERSAL - Accessories for tools

1218486

<https://www.phoenixcontact.com/us/products/1218486>

Holder for cleaving tool for multimode and singlemode connectors



FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/us/products/1089515>



FOC-TOOL-CLEAVER-UNIVERSAL - Distribution block

1218485

<https://www.phoenixcontact.com/us/products/1218485>

Cleaver for assembly of FO connectors



Technical data

Product properties

Product type	Assembly tool
--------------	---------------

Dimensions

Width	34.5 cm
Height	6.5 cm
Length	28 cm

Material specifications

Housing material	Plastic
------------------	---------

Cable/line

Cable type	for all common STB cable types, TB limited
------------	--

FO cable

Transmission medium	FO
---------------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

Mounting

Mounting type	mechanical splice
---------------	-------------------

FOC-TOOL-SET-GOF - Tool set



1089515

<https://www.phoenixcontact.com/us/products/1089515>

Classifications

ECLASS

ECLASS-15.0	21049090
ECLASS-13.0	21049090

ETIM

ETIM 10.0	EC000163
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FOC-TOOL-SET-GOF - Tool set



1089515

<https://www.phoenixcontact.com/us/products/1089515>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com