

# EB 10-10 - Insertion bridge




0203137

<https://www.phoenixcontact.com/us/products/0203137>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 10 mm, number of positions: 10, color: gray



## Commercial data

Item number	0203137
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z2X
Catalog page	Page 461 (C-1-2019)
GTIN	4017918098148
Weight per piece (including packing)	16.74 g
Weight per piece (excluding packing)	16.74 g
Customs tariff number	85366990
Country of origin	PL

# EB 10-10 - Insertion bridge



0203137

<https://www.phoenixcontact.com/us/products/0203137>

## Technical data

### Product properties

Product type	Insertion bridge
Number of positions	10
Pitch	10 mm
Potentials	10

### Dimensions

Pitch	10 mm
-------	-------

### Material specifications

Color	gray
Material	Cu
Flammability rating according to UL 94	V0
Insulating material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	Screw mounting
---------------	----------------

# EB 10-10 - Insertion bridge



0203137

<https://www.phoenixcontact.com/us/products/0203137>

## Classifications

### ECLASS

ECLASS-11.0	27141140
ECLASS-12.0	27141140
ECLASS-13.0	27250303

### ETIM

ETIM 9.0	EC000489
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# EB 10-10 - Insertion bridge



0203137

<https://www.phoenixcontact.com/us/products/0203137>

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)