

# EB 2- 6 - Insertion bridge

0201155

<https://www.phoenixcontact.com/us/products/0201155>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 6.2 mm, number of positions: 2, color: gray



## Commercial data

Item number	0201155
Packing unit	1 pc
Minimum order quantity	100 pc
Sales key	BE19
Product key	BE1Z2X
Catalog page	Page 467 (C-1-2019)
GTIN	4017918098278
Weight per piece (including packing)	1.133 g
Weight per piece (excluding packing)	1.129 g
Customs tariff number	85366990
Country of origin	CN

# EB 2- 6 - Insertion bridge



0201155

<https://www.phoenixcontact.com/us/products/0201155>

## Technical data

### Product properties

Product type	Insertion bridge
Number of positions	2
Pitch	6.2 mm

### Dimensions

Pitch	6.2 mm
-------	--------

### Material specifications

Color	gray
Material	CuZn (nickel-plated)
Flammability rating according to UL 94	V2
Insulating material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	Screw mounting
---------------	----------------

# EB 2- 6 - Insertion bridge



0201155

<https://www.phoenixcontact.com/us/products/0201155>

## Classifications

### ECLASS

ECLASS-11.0	27141140
ECLASS-12.0	27141140
ECLASS-13.0	27250303

### ETIM

ETIM 9.0	EC000489
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# EB 2- 6 - Insertion bridge



0201155

<https://www.phoenixcontact.com/us/products/0201155>

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)