

PSD-S AS BULB 5W - Incandescent lamp

2700142

<https://www.phoenixcontact.com/us/products/2700142>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bulb, 5 W, 24 V, BA15d base



Commercial data

Item number	2700142
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL11Z
Catalog page	Page 342 (C-8-2013)
GTIN	4046356491341
Weight per piece (including packing)	7.9 g
Weight per piece (excluding packing)	7.9 g
Customs tariff number	85392998
Country of origin	CN

PSD-S AS BULB 5W - Incandescent lamp



2700142

<https://www.phoenixcontact.com/us/products/2700142>

Technical data

Product properties

Type	Tube shape
Product type	Lamp
Base	B15d (bayonet)

Electrical properties

General

Input voltage	24 V
Source of light, power	5 W

Dimensions

Height	42 mm
Diameter	16 mm

Material specifications

Color	white
Material	Base: BA15d

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

Mounting

Mounting position	any
-------------------	-----

PSD-S AS BULB 5W - Incandescent lamp



2700142

<https://www.phoenixcontact.com/us/products/2700142>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700142>



EAC

Approval ID: RU *-DE.A*30.B.00237

PSD-S AS BULB 5W - Incandescent lamp



2700142

<https://www.phoenixcontact.com/us/products/2700142>

Classifications

ECLASS

ECLASS-12.0	27110631
ECLASS-11.0	27110631
ECLASS-13.0	27110631

ETIM

ETIM 9.0	EC000399
----------	----------

UNSPSC

UNSPSC 21.0	32151500
-------------	----------

PSD-S AS BULB 5W - Incandescent lamp



2700142

<https://www.phoenixcontact.com/us/products/2700142>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com