VS-PPC-J-M - Mounting adapter

1405390

https://www.phoenixcontact.com/gb/products/1405390

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting foot for the power H distributors, plastic



Mounting foot

Commercial data

Item number	1405390
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABNOHZ
Product key	ABNOHZ
GTIN	4046356419956
Weight per piece (including packing)	21.4 g
Weight per piece (excluding packing)	19.3 g
Customs tariff number	85389099
Country of origin	DE

Technical data

Product properties

Product type	Adapter plate

Connection data

Connection method	Screw connection

Dimensions

Width	16.1 mm
Height	48 mm
Length	115 mm

Material specifications

Material	PA 6.6
Flammability rating according to UL 94	V0

Cable/line

External cable diameter	5 mm ... 8 mm
Cable cross section	0.13 mm²

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20

Classifications

ECLASS

ECLASS-13.0	27440201
ECLASS-15.0	27440201

ETIM

ETIM 10.0	EC002309

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.151 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk