

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection



1019676

<https://www.phoenixcontact.com/us/products/1019676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink splice protection, design: Straight, degree of protection: IP20, cable outlet: above and below, color: transparent

Product description

Shrink splice protection

Your advantages

- No attenuating effects on the fusion splice
- Mechanical protection for fusion splices
- Bellcore GR-1380-CORE (Telcordia)
- BT (British Telecom)

Commercial data

Item number	1019676
Packing unit	12 pc
Minimum order quantity	12 pc
Sales key	AB15
Product key	ABNGAZ
GTIN	4055626701196
Weight per piece (including packing)	0.263 g
Weight per piece (excluding packing)	0.07 g
Customs tariff number	39269097
Country of origin	DE

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection



1019676

<https://www.phoenixcontact.com/us/products/1019676>

Technical data

Notes

Order information:	Splice protection for FDX 20 splice boxes
Assembly note	120°C for 30 seconds (type-dependent)

Product properties

Housing type	Fiber optic
Cable outlet	above and below

Dimensions

Height	1.3 mm
Depth	0.5 mm
Length	30 mm

Material specifications

Color	transparent
Material	Ethylene-vinyl acetate (EVA)

Cable/line

Cable type	Fiberglass
External cable diameter	250 µm (Includes primary coating)

FO cable

Transmission medium	FO
---------------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-40 °C ... 70 °C (according to DIN EN 61300-2)

Mounting

Mounting type	Shrink splice protection
Assembly note	Shrink splice protection clicks into the splice holder

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection



1019676

<https://www.phoenixcontact.com/us/products/1019676>

Classifications

ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

ETIM

ETIM 10.0	EC003626
-----------	----------

UNSPSC

UNSPSC 21.0	26121650
-------------	----------

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection



1019676

<https://www.phoenixcontact.com/us/products/1019676>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com