

# UM-SE - Lateral element



2955593

<https://www.phoenixcontact.com/us/products/2955593>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Side element, for closing both ends of the base element UM-BEFE



## Commercial data

Item number	2955593
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDDA
Catalog page	Page 762 (C-1-2013)
GTIN	4017918085568
Weight per piece (including packing)	3.16 g
Weight per piece (excluding packing)	3.08 g
Customs tariff number	85369010
Country of origin	PL

# UM-SE - Lateral element



2955593

<https://www.phoenixcontact.com/us/products/2955593>

## Technical data

### Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM ST SE
Type	Lateral element
Ventilation openings present	no

### Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	V0
Housing material	Polyamide
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

# UM-SE - Lateral element

2955593

<https://www.phoenixcontact.com/us/products/2955593>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2955593>



**UL Recognized**

Approval ID: E240868

# UM-SE - Lateral element

2955593

<https://www.phoenixcontact.com/us/products/2955593>



## Classifications

### ECLASS

ECLASS-11.0	27182701
ECLASS-13.0	27190602

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM-SE - Lateral element



2955593

<https://www.phoenixcontact.com/us/products/2955593>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)