

TP-UK 35 - Separating plate

3008096

<https://www.phoenixcontact.com/us/products/3008096>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Separating plate, width: 7.5 mm, height: 50 mm, color: gray



Commercial data

Item number	3008096
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z1X
Catalog page	Page 213 (CL-2005)
GTIN	4017918091590
Weight per piece (including packing)	5.571 g
Weight per piece (excluding packing)	5.009 g
Customs tariff number	39269097
Country of origin	DE

TP-UK 35 - Separating plate



3008096

<https://www.phoenixcontact.com/us/products/3008096>

Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray
Flammability rating according to UL 94	V0

Dimensions

Width	7.5 mm
Height	50 mm
Depth	52 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

TP-UK 35 - Separating plate

3008096

<https://www.phoenixcontact.com/us/products/3008096>



Classifications

ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TP-UK 35 - Separating plate

3008096

<https://www.phoenixcontact.com/us/products/3008096>



Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com