

# WIREFOX 10 - Stripping tool



1212150

<https://www.phoenixcontact.com/us/products/1212150>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

## Product description

Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212152 WIREFOX 10/SB

## Your advantages

- Flexible, adjustable limit stop for the stripping length
- Practical integrated wire cutter
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

## Commercial data

Item number	1212150
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3121
Catalog page	Page 407 (C-3-2019)
GTIN	4046356454407
Weight per piece (including packing)	210.5 g
Weight per piece (excluding packing)	201.5 g
Customs tariff number	82032000
Country of origin	SE

# WIREFOX 10 - Stripping tool



1212150

<https://www.phoenixcontact.com/us/products/1212150>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Stripping tool

Application

Abisolieren von Leitungen und Leiter

### Connection data

#### Conductor connection

Cross section range, metric

0.02 mm<sup>2</sup> ... 10 mm<sup>2</sup> (Stripping range)

1.5 mm<sup>2</sup> (Cutting zone)

Cross section range AWG

34 ... 8 (Stripping range)

16 (Cutting zone)

Stripping length

2 mm ... 18 mm

### Dimensions

Width

20 mm

Height

90 mm

Length

191 mm

### Material specifications

Color

black/green

# WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212150>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



## Classifications

### ECLASS

ECLASS-11.0	21043706
ECLASS-12.0	21043706
ECLASS-13.0	21043706

### ETIM

ETIM 9.0	EC002109
----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



## Accessories

### WIREFOX 10/SB - Spare knife

1212152

<https://www.phoenixcontact.com/us/products/1212152>



Replacement blade for WIREFOX 10, for cables and conductors of 0.02 - 10 mm<sup>2</sup>

---

### WIREFOX 10/WS - Replacement limit stop

1200285

<https://www.phoenixcontact.com/us/products/1200285>



Replacement limit stop

# WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



## WIREFOX 10/CJ - Replacement retaining jaw

1200286

<https://www.phoenixcontact.com/us/products/1200286>

Replacement clamping jaws for WIREFOX 4, WIREFOX 6SC, and WIREFOX 10



---

## WIREFOX 4/SB - Spare knife

1212151

<https://www.phoenixcontact.com/us/products/1212151>

Replacement blade for WIREFOX 4, for cables and conductors (especially for rubber and silicone insulations) of 0.1 - 4 mm<sup>2</sup>



# WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



## WIREFOX 6SC/SB - Spare knife

1212314

<https://www.phoenixcontact.com/us/products/1212314>



Replacement blade for WIREFOX 6SC, for cables and conductors (especially for cables protected against short circuits and ground leakages) 1.5 - 6 mm<sup>2</sup>

---

## WIREFOX 16/SB - Spare knife

1212153

<https://www.phoenixcontact.com/us/products/1212153>



Replacement blade for WIREFOX 16, for cables and conductors of 4 - 16 mm<sup>2</sup>

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)