

CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising WIREFOX 10, WIREFOX 16/SB, CRIMPFOX DUO 16S, AI SORTI BOX RD, AI SORTI BOX ANT, TOOL-KIT STANDARD EMPTY

Product description

Tool set, equipped

Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools

Commercial data

Item number	1367687
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4063151722128
Weight per piece (including packing)	1,102 g
Weight per piece (excluding packing)	1,100 g
Customs tariff number	82060000
Country of origin	DE

CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

Set consists of

CRIMPFOX DUO 16S - Crimping pliers

1202877

<https://www.phoenixcontact.com/us/products/1202877>



Crimping pliers, contact type: insulated and uninsulated ferrules, standards/regulations: DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F, cross-section, minimum: 0.14 mm², cross-section, maximum: 16 mm², for TWIN ferrules up to 2 mm² x 6 mm², automatic cross-section adjustment, rotating dies, lateral and front entry, crimping: square

WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

CRIMPFOX DUO 16S SET - Tool set

1367687

<https://www.phoenixcontact.com/us/products/1367687>



WIREFOX 16/SB - Spare knife

1212153

<https://www.phoenixcontact.com/us/products/1212153>



Replacement blade for WIREFOX 16, for cables and conductors of 4 - 16 mm²

AI SORTI BOX RD - Range box

3202960

<https://www.phoenixcontact.com/us/products/3202960>



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

CRIMPFOX DUO 16S SET - Tool set

1367687

<https://www.phoenixcontact.com/us/products/1367687>



AI SORTI BOX ANT - Range box

3202973

<https://www.phoenixcontact.com/us/products/3202973>



Sorti-box, equipped with ferrules in accordance with DIN 46228-4, CSA-certified, 50 pcs. of AI 4-10 GY, 20 pcs. each of AI 6-12 YE, AI 10-12 RD, 10 pcs. of AI 16-12 BU

TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

<https://www.phoenixcontact.com/us/products/1212423>



Tool box, unequipped

CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

Technical data

Notes

General	DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F
---------	---

Product properties

Product type	Tool set
Type of packaging	Bag
Compression	Square crimp

Crimping position 1

Min. cross section	16 mm ²
Max. cross section	0.14 mm ²
AWG min	26
AWG max	6

Electrical properties

Fuse	DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F
------	---

Dimensions

Width	65 mm
Height	315 mm
Length	165 mm

Material specifications

Color	black
-------	-------

CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

Classifications

ECLASS

ECLASS-11.0	21045003
ECLASS-12.0	21045003
ECLASS-13.0	21045003

ETIM

ETIM 9.0	EC000149
----------	----------

UNSPSC

UNSPSC 21.0	27113200
-------------	----------

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com