

ESL 29X8 - Insert strip

0808257

<https://www.phoenixcontact.com/us/products/0808257>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, CMS-P1-PLOTTER, perforated, mounting type: insert, lettering field size: 29 x 8 mm, Number of individual labels: 174



Your advantages

- Phoenix Contact: KMK, KMK 2, KMK HP (29x8), and KMK UV (29x8) plastic cable markers
- Due to their special shape, the ESL-29x8 insert labels fit perfectly into the KMK ... (29x8) marker carriers
- The material file can be downloaded under the PROJECT COMPLETE software under Downloads – “Software update – Marking”

Commercial data

Item number	0808257
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	BG12
Product key	BG2314
Catalog page	Page 235 (C-3-2019)
GTIN	4017918171490
Weight per piece (including packing)	14.26 g
Weight per piece (excluding packing)	12.616 g
Customs tariff number	39206219
Country of origin	DE

Technical data

Notes

General	Print image may vary depending on laser printer
---------	---

Product properties

Product type	Terminal marking
--------------	------------------

Marking

Number of individual labels	174
Number of individual labels per row	6

Dimensions

Width	29 mm
Length	8 mm

Material specifications

Color	white
Material	Polyester foil
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2011 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

ESL 29X8 - Insert strip



0808257

<https://www.phoenixcontact.com/us/products/0808257>

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	insert
---------------	--------

ESL 29X8 - Insert strip



0808257

<https://www.phoenixcontact.com/us/products/0808257>

Classifications

ECLASS

ECLASS-11.0	27281106
ECLASS-12.0	27281106
ECLASS-13.0	27281106

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

ESL 29X8 - Insert strip

0808257

<https://www.phoenixcontact.com/us/products/0808257>




Accessories

PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/us/products/0804499>

Marking plotter for the entire portfolio of UC marking materials and materials in sheet and strip format.



KMK - Plastic cable markers

1005208

<https://www.phoenixcontact.com/us/products/1005208>

Plastic cable markers, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter range: 10 ... 25 mm, lettering field size: 29 x 8 mm



ESL 29X8 - Insert strip

0808257

<https://www.phoenixcontact.com/us/products/0808257>



KMK 2 - Plastic cable markers

1005266

<https://www.phoenixcontact.com/us/products/1005266>

Plastic cable markers, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 6 mm, lettering field size: 29 x 8 mm



KMK HP (29X8) - Cable marker carrier

0830721

<https://www.phoenixcontact.com/us/products/0830721>

Cable marker carrier, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 6 mm, lettering field size: 29 x 8 mm



ESL 29X8 - Insert strip

0808257

<https://www.phoenixcontact.com/us/products/0808257>



KMK UV (29X8) - Cable marker carrier

1014107

<https://www.phoenixcontact.com/us/products/1014107>

Cable marker carrier, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 6 mm, lettering field size: 29 x 8 mm



Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com