

# TSD 04 SAC - Torque screwdriver



1208429

<https://www.phoenixcontact.com/us/products/1208429>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

## Your advantages

- TSD ... SAC torque screwdrivers with a range of preset torques from 0.2 Nm to 2.5 Nm
- For the TSD-M... torque screwdrivers the torque can be set individually
- The TSD-M... adapters can accommodate the various nuts
- Wide range of SAC... nuts for various different applications

## Commercial data

Item number	1208429
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH314A
Catalog page	Page 460 (C-3-2019)
GTIN	4046356014519
Weight per piece (including packing)	90.9 g
Weight per piece (excluding packing)	90.9 g
Customs tariff number	82054000
Country of origin	CZ

# TSD 04 SAC - Torque screwdriver



1208429

<https://www.phoenixcontact.com/us/products/1208429>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Type	Hexagonal SW4
Product type	Torque tool

### Connection data

Torque range	0.4 Nm ... 0.4 Nm $\pm$ 10 %
Output	External hexagonal

### Dimensions

Width	37 mm
Blade width	0 mm
Blade height	100 mm
Length	205 mm
Blade thickness	0 mm

### Material specifications

Color	black
-------	-------

# TSD 04 SAC - Torque screwdriver



1208429

<https://www.phoenixcontact.com/us/products/1208429>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1208429>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# TSD 04 SAC - Torque screwdriver



1208429

<https://www.phoenixcontact.com/us/products/1208429>

## Classifications

### ECLASS

ECLASS-11.0	21040417
ECLASS-12.0	21040417
ECLASS-13.0	21040417

### ETIM

ETIM 9.0	EC011814
----------	----------

### UNSPSC

UNSPSC 21.0	27111700
-------------	----------

# TSD 04 SAC - Torque screwdriver

1208429

<https://www.phoenixcontact.com/us/products/1208429>



## Accessories

### SAC BIT M12-D15 - Tool

1208432

<https://www.phoenixcontact.com/us/products/1208432>



Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, with a knurl diameter of 15 mm, for 4 mm hexagonal drive

---

### SACC BIT M12-D20 - Tool

1208445

<https://www.phoenixcontact.com/us/products/1208445>



Nut for assembling M12 connectors for assembly with a knurl diameter of 20 mm, for 4 mm hexagonal drive

# TSD 04 SAC - Torque screwdriver

1208429

<https://www.phoenixcontact.com/us/products/1208429>



## SAC BIT M12-W14 - Tool

1212513

<https://www.phoenixcontact.com/us/products/1212513>

Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, with a hexagonal knurl wrench size of 14 mm, with 4 mm hexagonal drive



---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)