

OCS FOOT SET - Wall bracket



1471777

<https://www.phoenixcontact.com/us/products/1471777>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting foot, set of 4 pieces incl. screws for all housing sizes, material: polycarbonate, color: light gray



Your advantages

- Internationally certified housing system
- Special plastic ensures safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial data

Item number	1471777
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC04
Product key	ACFDBZ
GTIN	4063151880859
Weight per piece (including packing)	85 g
Weight per piece (excluding packing)	85 g
Customs tariff number	39269097
Country of origin	EE

OCS FOOT SET - Wall bracket



1471777

<https://www.phoenixcontact.com/us/products/1471777>

Technical data

Notes

General	Only use the screws supplied for mounting.
General	You can mount the mounting feet in 3 different positions.
General	Secure the mounting feet or flanges using the screws provided. If mounting the housing on a wall, select the appropriate screw type for the wall construction.

Product properties

Product type	Mounting material
Housing type	Outdoor housing
Housing series	OCS

Dimensions

Width	45 mm
Height	65 mm
Depth	10 mm

Material specifications

Flammability rating according to UL 94	V2
Insulating material	PC
Surface characteristics	untreated
Housing material	Polycarbonate

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

Mounting

Mounting type	Mast mounting or wall mounting
---------------	--------------------------------

OCS FOOT SET - Wall bracket



1471777

<https://www.phoenixcontact.com/us/products/1471777>

Classifications

ECLASS

ECLASS-11.0	27182702
ECLASS-13.0	27190605

ETIM

ETIM 9.0	EC001031
----------	----------

OCS FOOT SET - Wall bracket

1471777

<https://www.phoenixcontact.com/us/products/1471777>



Accessories

SZK PH2 VDE - Screwdriver

1205163

<https://www.phoenixcontact.com/us/products/1205163>



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

SF-BIT SET - Tool set

1212545

<https://www.phoenixcontact.com/us/products/1212545>



Bit set, with SF-UBH universal bit holder, with 25 mm long bladed/crosshead bits (PZ and PH), 10-part, in compact plastic box

OCS FOOT SET - Wall bracket

1471777

<https://www.phoenixcontact.com/us/products/1471777>



SF-PH 2-100 - Screwdriver

1212560

<https://www.phoenixcontact.com/us/products/1212560>



Screwdriver, PH crosshead (lasered), uninsulated, size: PH 2 x 100, 2-component grip, with non-slip grip

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com