

OCS MOUNT 0806 SET - Wall bracket



1471778

<https://www.phoenixcontact.com/us/products/1471778>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting plate, set of 2 pieces incl. screws for housing size of 8" x 6", material: polycarbonate, color: light gray



Your advantages

- Internationally certified housing system
- Special plastic ensures safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1471778 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC04 |
| Product key | ACFDBZ |
| GTIN | 4063151876388 |
| Weight per piece (including packing) | 0.108 kg |
| Weight per piece (excluding packing) | 0.097 kg |
| Customs tariff number | 39269097 |
| Country of origin | EE |

OCS MOUNT 0806 SET - Wall bracket



1471778

<https://www.phoenixcontact.com/us/products/1471778>

Technical data

Notes

| | |
|---------|--|
| General | Only use the screws supplied for mounting. |
| General | Secure the mounting feet or flanges using the screws provided. If mounting the housing on a wall, select the appropriate screw type for the wall construction. |

Product properties

| | |
|----------------|-------------------|
| Product type | Mounting material |
| Housing type | Outdoor housing |
| Housing series | OCS |

Dimensions

| | |
|--------|--------|
| Width | 65 mm |
| Height | 144 mm |
| Depth | 8 mm |

Material specifications

| | |
|--|---------------|
| Flammability rating according to UL 94 | V2 |
| Insulating material | PC |
| Surface characteristics | untreated |
| Housing material | Polycarbonate |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

OCS MOUNT 0806 SET - Wall bracket



1471778

<https://www.phoenixcontact.com/us/products/1471778>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27182702 |
| ECLASS-13.0 | 27190605 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001031 |
|----------|----------|

OCS MOUNT 0806 SET - Wall bracket



1471778

<https://www.phoenixcontact.com/us/products/1471778>

Mandatory accessories

OCS HP 080604 GY7035 - Electronic housing

1471770

<https://www.phoenixcontact.com/us/products/1471770>



Outdoor housing, color: light gray, dimensions: 8" x 6" x 4", incl. corner inlays, cover plugs, screws, cover: light gray, plastic latch, material: PC UV-stabilized

OCS HP 080604 TRANS - Electronic housing

1471772

<https://www.phoenixcontact.com/us/products/1471772>



Outdoor housing, color: light gray, dimensions: 8" x 6" x 4", incl. corner inlays, cover plugs, screws, cover: transparent, plastic latch, material: PC UV-stabilized

Accessories

OCS MOUNT 0806 SET - Wall bracket

1471778

<https://www.phoenixcontact.com/us/products/1471778>



SZK PH2 VDE - Screwdriver

1205163

<https://www.phoenixcontact.com/us/products/1205163>



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

SF-BIT SET - Tool set

1212545

<https://www.phoenixcontact.com/us/products/1212545>



Bit set, with SF-UBH universal bit holder, with 25 mm long bladed/crosshead bits (PZ and PH), 10-part, in compact plastic box

OCS MOUNT 0806 SET - Wall bracket

1471778

<https://www.phoenixcontact.com/us/products/1471778>



SF-PH 2-100 - Screwdriver

1212560

<https://www.phoenixcontact.com/us/products/1212560>



Screwdriver, PH crosshead (lasered), uninsulated, size: PH 2 x 100, 2-component grip, with non-slip grip

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com