

PHT22-FLD-BU - Button

1108696

<https://www.phoenixcontact.com/gb/products/1108696>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Illuminated flat button, 22 mm, circular, blue, self-locking



Your advantages

- 22 mm illuminated button – compact and modern
- Self-retaining (latching) – ideal for switching functions
- With integrated lighting option for clear status display
- Designed for modular combination with PHT22 contact and LED modules
- Quick mounting in the control cabinet/control panel

Commercial data

Item number	1108696
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE6122
Product key	BE6122
GTIN	4063151015787
Weight per piece (including packing)	19.6 g
Weight per piece (excluding packing)	17.3 g
Customs tariff number	85389099
Country of origin	CN

Technical data

Product properties

Product type	Actuator
--------------	----------

Dimensions

Width	29.6 mm
Height	29.6 mm

Material specifications

Color	blue
-------	------

Environmental and real-life conditions

Degree of protection (IP code)

Degree of protection	IP66
----------------------	------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

Standards and regulations

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

Mounting

Mounting type	Panel mount
Tightening torque	1 Nm ... 1.2 Nm

PHT22-FLD-BU - Button



1108696

<https://www.phoenixcontact.com/gb/products/1108696>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1108696>



cULus Listed

Approval ID: E172140



CCC

Approval ID: 2024010305697836

Functional Safety

Approval ID: R CN21G3UE 001

PHT22-FLD-BU - Button



1108696

<https://www.phoenixcontact.com/gb/products/1108696>

Classifications

ECLASS

ECLASS-15.0	27371210
ECLASS-13.0	27371210

PHT22-FLD-BU - Button



1108696

<https://www.phoenixcontact.com/gb/products/1108696>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk