

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/gb/products/1212039>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 10 mm² ... 25 mm², lateral entry, WM crimp

Your advantages

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25 %

Commercial data

Item number	1212039
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH3131
Product key	BH3131
GTIN	4046356453905
Weight per piece (including packing)	681.4 g
Weight per piece (excluding packing)	681.4 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX 25R - Crimping pliers

1212039

<https://www.phoenixcontact.com/gb/products/1212039>



Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	WM crimp
Product property	Low grip span
	Up to 25% lower actuation force

Crimping position 1

Max. cross section	10 mm ²
AWG min	8
AWG max	4

Crimping position 2

Max. cross section	16 mm ²
AWG max	6

Crimping position 3

Max. cross section	25 mm ²
AWG max	4

Connection data

Conductor connection

Cross section range, metric	10 mm ² ... 25 mm ²
Cross section range AWG	8 ... 4

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

Material specifications

Color	black
-------	-------

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/gb/products/1212039>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1212039>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/gb/products/1212039>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/gb/products/1212039>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk