

FBP-3/4SL - Blind plug

1030010

<https://www.phoenixcontact.com/gb/products/1030010>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Blind plug, number of positions: 4, color: transparent



Commercial data

Item number	1030010
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE6113
Product key	BE6113
GTIN	4055626532073
Weight per piece (including packing)	39.8 g
Weight per piece (excluding packing)	35 g
Customs tariff number	39162000
Country of origin	PL

FBP-3/4SL - Blind plug



1030010

<https://www.phoenixcontact.com/gb/products/1030010>

Technical data

Product properties

Product type	Blind plug
Product family	FAME 3 SL
Number of positions	4

Dimensions

Width	74.1 mm
Height	65 mm
Depth	32 mm

Material specifications

Color	transparent
Flammability rating according to UL 94	V0
Insulating material	PVC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FBP-3/4SL - Blind plug



1030010

<https://www.phoenixcontact.com/gb/products/1030010>

Classifications

ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

ETIM

ETIM 10.0	EC002555
-----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

FBP-3/4SL - Blind plug



1030010

<https://www.phoenixcontact.com/gb/products/1030010>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk