# RIF-2-BPT/4X21 - Relay base

2900934

https://www.phoenixcontact.com/gb/products/2900934

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay base RIF-2..., for industrial relay with 2 or 4 changeover contacts, Push-in connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

## Commercial data

| | |
|---|---|
| Item number | 2900934 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | DK6523 |
| Product key | DK6523 |
| GTIN | 4046356733175 |
| Weight per piece (including packing) | 69.15 g |
| Weight per piece (excluding packing) | 62.825 g |
| Customs tariff number | 85366990 |
| Country of origin | CN |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Relay socket |
| Product family | RIFLINE complete |
| Set comprises | 2903304 RIF-2-RPT-LV-230AC/4X21 |
| | 2903305 RIF-2-RPT-LV-120AC/4X21 |
| | 2903306 RIF-2-RPT-LV-24AC/4X21 |
| | 2903308 RIF-2-RPT-LDP-24DC/4X21 |
| | 2903310 RIF-2-RPT-LV-230AC/2X21 |
| | 2903311 RIF-2-RPT-LV-120AC/2X21 |
| | 2903313 RIF-2-RPT-LV-24AC/2X21 |
| | 2903315 RIF-2-RPT-LDP-24DC/2X21 |
| | 2908332 RIF-2-RPT-LDP-24DC/4X21 AU |

### Electrical properties

| | |
|---|---|
| Nominal voltage $U_N$ | 250 V AC/DC |
| Nominal current $I_N$ | max. 12 A (Depends on application/assembly) |
| Protective circuit | depending on the selected input/suppressor modules |

### Connection data

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.14 mm² ... 1.5 mm² |
| Conductor cross-section flexible | 0.14 mm² ... 1.5 mm² |
| | 0.14 mm² ... 1.5 mm² (Ferrule with plastic sleeve) |
| | 0.14 mm² ... 1 mm² (Ferrule with plastic sleeve, two conductors on double terminal block) |
| Conductor cross-section AWG | 26 ... 16 (solid) |
| | 26 ... 16 (flexible) |

### Dimensions

Item dimensions

| | |
|---|---|
| Width | 31 mm |
| Height | 96 mm |
| Depth (Retaining bracket) | 75 mm (with retaining bracket) |

Drill hole

| | |
|---|---|
| Diameter | 3.2 mm |

### Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V2 (Housing) |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 85 °C (Depends on application/assembly) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Approvals

Corrosive gas test

| | |
|---|---|
| Identification | ISA-S71.04. G3 Harsh Group |
| | EN 60068-2-60 |

## Mounting

| | |
|---|---|
| Mounting type | DIN rail mounting |
| Mounting position | any |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/2900934

**CSA**
Approval ID: 76787

**UL Recognized**
Approval ID: FILE E 113228

**EAC**
Approval ID: RU D-DE.B*00573/18

**DNV**
Approval ID: TAA000018V

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27371603 |
| ECLASS-15.0 | 27371603 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001456 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39122300 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk