

UPS-BAT-KIT/PB/2X12V/12AH - Uninterruptible power supply replacement battery



1283121

<https://www.phoenixcontact.com/gb/products/1283121>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement battery, VRLA-AGM, 2x12 V DC, 12 Ah



Commercial data

Item number	1283121
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CMUEV3
Product key	CMUEV3
GTIN	4063151488130
Weight per piece (including packing)	8,111 g
Weight per piece (excluding packing)	8,111 g
Customs tariff number	85072080
Country of origin	CN

UPS-BAT-KIT/PB/2X12V/12AH - Uninterruptible power supply replacement battery



1283121

<https://www.phoenixcontact.com/gb/products/1283121>

Technical data

Notes

General

Note on the battery	This product contains a battery with a limited shelf life that must be charged every few months. The product packaging indicates when the battery must be started up or recharged. The general shelf life can be found in the energy storage devices area under "Latest startup".
---------------------	---

Energy storage

Input

Input voltage	2x 12 V
Nominal capacity	12 Ah

General

Battery type	BB Battery BP 12-12FR
Battery technology	VRLA-AGM
IQ-Technology	no
Latest startup date (battery only)	12 Months (-20 °C ... 20 °C) 9 Months (25 °C) 6 Months (30 °C)

Product properties

Product type	Battery
Product family	Replacement battery
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations.

Insulation characteristics

Protection class	III
Degree of pollution	2

Dimensions

Item dimensions

Width	200 mm
Height	153 mm
Depth	100 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

UPS-BAT-KIT/PB/2X12V/12AH - Uninterruptible power supply replacement battery



1283121

<https://www.phoenixcontact.com/gb/products/1283121>

	IP20
Ambient temperature (storage/transport)	-20 °C ... 40 °C
Ambient temperature (charge)	0 °C ... 40 °C
Ambient temperature (discharge)	-20 °C ... 50 °C
Max. permissible relative humidity (operation)	≤ 95 %

Ex data

Suited for EX-applications	no
----------------------------	----

UPS-BAT-KIT/PB/2X12V/12AH - Uninterruptible power supply replacement battery



1283121

<https://www.phoenixcontact.com/gb/products/1283121>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1283121>



GOST-R

Approval ID: ROSS DE.BL08.D00191

UPS-BAT-KIT/PB/2X12V/12AH - Uninterruptible power supply replacement battery



1283121

<https://www.phoenixcontact.com/gb/products/1283121>

Classifications

ECLASS

ECLASS-13.0	27059090
ECLASS-15.0	27050492

ETIM

ETIM 10.0	EC002839
-----------	----------

UNSPSC

UNSPSC 21.0	26111700
-------------	----------

UPS-BAT-KIT/PB/2X12V/12AH - Uninterruptible power supply replacement battery



1283121

<https://www.phoenixcontact.com/gb/products/1283121>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

China RoHS

Environment friendly use period (EFUP)	EFUP-8 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	---

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0d9b6175-17c9-47aa-9cd1-a6910610b434

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk