

# PHT22-MBL60-BU - Button

1108467

<https://www.phoenixcontact.com/gb/products/1108467>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mushroom button head, 22 mm, circular, button head diameter: 60 mm, blue, self-locking



## Your advantages

- 22 mm mushroom button (60 mm) – extra large and eye-catching
- Self-retaining (latching) – ideal for safe switching functions
- Extra large actuating surface for fast, intuitive operation
- Robust industrial design for durable use
- Designed for modular combination with PHT22 contact and LED modules

## Commercial data

Item number	1108467
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE6122
Product key	BE6122
GTIN	4063151014506
Weight per piece (including packing)	33.2 g
Weight per piece (excluding packing)	30.9 g
Country of origin	Information on the country of origin is provided with the delivery.

## Technical data

### Product properties

Product type	Actuator
--------------	----------

### Dimensions

Width	60 mm
Height	60 mm

### Material specifications

Color	blue
-------	------

### Environmental and real-life conditions

#### Degree of protection (IP code)

Degree of protection	IP66
----------------------	------

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

### Mounting

Mounting type	Panel mount
Tightening torque	1 Nm ... 1.2 Nm

# PHT22-MBL60-BU - Button



1108467

<https://www.phoenixcontact.com/gb/products/1108467>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1108467>



**cULus Listed**

Approval ID: E172140



**CCC**

Approval ID: 2024010305697836

# PHT22-MBL60-BU - Button



1108467

<https://www.phoenixcontact.com/gb/products/1108467>

## Classifications

### ECLASS

ECLASS-13.0	27371403
ECLASS-15.0	27371403

### ETIM

ETIM 10.0	EC000216
-----------	----------

# PHT22-MBL60-BU - Button



1108467

<https://www.phoenixcontact.com/gb/products/1108467>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)