

PHT22-MBR-WH - Button

1108480

<https://www.phoenixcontact.com/gb/products/1108480>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mushroom button, 22 mm, circular, button head diameter: 40 mm, white, self-resetting



Your advantages

- 22 mm mushroom button (40 mm) – easy to grasp and eye-catching
- Spring return (momentary action) – ideal for pulse/start functions
- Large actuating surface for fast, intuitive operation
- Robust industrial design for durable use
- Designed for modular combination with PHT22 contact and LED modules

Commercial data

Item number	1108480
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE6122
Product key	BE6122
GTIN	4063151014452
Weight per piece (including packing)	26.1 g
Weight per piece (excluding packing)	23.7 g
Customs tariff number	85389099
Country of origin	Information on the country of origin is provided with the delivery.

Technical data

Product properties

Product type	Actuator
--------------	----------

Dimensions

Width	40 mm
Height	40 mm

Material specifications

Color	white
-------	-------

Environmental and real-life conditions

Degree of protection (IP code)

Degree of protection	IP66
----------------------	------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

Standards and regulations

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

Mounting

Mounting type	Panel mount
Tightening torque	1 Nm ... 1.2 Nm

PHT22-MBR-WH - Button



1108480

<https://www.phoenixcontact.com/gb/products/1108480>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1108480>



cULus Listed

Approval ID: E172140



CCC

Approval ID: 2024010305697836

Functional Safety

Approval ID: R CN21G3UE 001

PHT22-MBR-WH - Button



1108480

<https://www.phoenixcontact.com/gb/products/1108480>

Classifications

ECLASS

ECLASS-13.0	27371403
ECLASS-15.0	27371403

ETIM

ETIM 10.0	EC000216
-----------	----------

PHT22-MBR-WH - Button



1108480

<https://www.phoenixcontact.com/gb/products/1108480>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk