

PRC 20-CCF 0,5-2,5 - Crimp contact

1468461

<https://www.phoenixcontact.com/gb/products/1468461>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, Range of articles: PRC 20, color: silver, min. conductor cross-section: 0.5 mm², max. conductor cross-section: 2.5 mm², rated current: 20 A, Connection method: Crimp connection, For assembly notes, please refer to the packing slip

Your advantages

- More space on the device front with current transmission up to 20 A in a minimum amount of space
- Duo-Unlock technology for greater flexibility during installation and maintenance
- Reliable use under extreme ambient conditions with high degrees of protection and impact resistance
- Simple handling with proven crimp or screw connection technology
- Mechanical and color coding for quick and error-free startup

Commercial data

Item number	1468461
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABLHZA
Product key	ABLHZA
GTIN	4063151866556
Weight per piece (including packing)	3.62 g
Weight per piece (excluding packing)	3.256 g
Country of origin	DE

PRC 20-CCF 0,5-2,5 - Crimp contact



1468461

<https://www.phoenixcontact.com/gb/products/1468461>

Technical data

Notes

Note on application	For assembly notes, please refer to the packing slip
---------------------	--

Product properties

Product type	Crimp contact
Product family	PRC 20

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Stripping length of the individual wire	8 mm

Material specifications

Color (Complete item)	silver-colored
-----------------------	----------------

Electrical properties

Rated current	20 A (With 2.5 mm ² conductor cross-section in accordance with IEC 61535)
	20 A (With 2.5 mm ² conductor cross-section in accordance with IEC 61984)
	20 A (With 2.5 mm ² /AWG 14, in accordance with UL 2238)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	500
-----------------------------	-----

PRC 20-CCF 0,5-2,5 - Crimp contact



1468461

<https://www.phoenixcontact.com/gb/products/1468461>

Classifications

ECLASS

ECLASS-13.0	27440691
ECLASS-15.0	27440691

ETIM

ETIM 10.0	EC002863
-----------	----------

PRC 20-CCF 0,5-2,5 - Crimp contact



1468461

<https://www.phoenixcontact.com/gb/products/1468461>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk