

EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/gb/products/2947750>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Custom circuit module, consisting of housing, MKDS 3 connection terminal blocks and PCB



Commercial data

Item number	2947750
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	ACHCBA
Product key	ACHCBA
GTIN	4017918082864
Weight per piece (including packing)	22.53 g
Weight per piece (excluding packing)	22.28 g
Customs tariff number	85369010
Country of origin	DE

EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/gb/products/2947750>




Technical data

Product properties

Product type	Stackable housing set
Housing type	Component housing
Housing series	EMG
Product family	EMG
Number of positions	4
Pitch	5 mm
Ventilation openings present	no

Dimensions

Dimensional drawing	
Width	10 mm
Installed height	47.5 mm
Height NS 35/7,5	55 mm
	100 mm
Depth	75 mm
Length	75 mm
Pitch	5 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PC (glass-fiber reinforced)
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 125 °C

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/gb/products/2947750>



Drawings

Dimensional drawing



1 = Top edge of the PCB

B = Housing width


EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/gb/products/2947750>



Dimensional drawing



Pitch 5 mm

a = Area for mounting components, 38 mm in the hood

b = Area for mounting components, 45 mm in the housing

EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/gb/products/2947750>



Classifications

ECLASS

ECLASS-15.0	27190301
ECLASS-13.0	27190301

ETIM

ETIM 10.0	EC001031
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EMG 10-B2 - Electronics housing



2947750

<https://www.phoenixcontact.com/gb/products/2947750>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.485 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk