

FUSE 10A/32V FK1 - Fuse

2908364

<https://www.phoenixcontact.com/gb/products/2908364>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fuse, nominal current: 10 A, length: 11.9 mm, width: 3.8 mm, height: 16.2 mm



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2908364 |
| Packing unit | 2 pc |
| Minimum order quantity | 2 pc |
| Note | Made to order (non-returnable) |
| Sales key | CMUEZ9 |
| Product key | CMUEZ9 |
| GTIN | 4055626296012 |
| Weight per piece (including packing) | 2 g |
| Weight per piece (excluding packing) | 1.67 g |
| Customs tariff number | 85361010 |
| Country of origin | CN |

FUSE 10A/32V FK1 - Fuse

2908364

<https://www.phoenixcontact.com/gb/products/2908364>



Technical data

Product properties

| | |
|--------------|------|
| Product type | Fuse |
|--------------|------|

Electrical properties

| | |
|-------------------------|---|
| Tripping characteristic | C |
| Nominal current I_N | 10 A |
| Fuse | Fuse (flat-type fuse for automotive applications) |

FUSE 10A/32V FK1 - Fuse

2908364

<https://www.phoenixcontact.com/gb/products/2908364>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2908364>



EAC

Approval ID: RU C-DE.BL08.B.00724

FUSE 10A/32V FK1 - Fuse

2908364

<https://www.phoenixcontact.com/gb/products/2908364>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27142008 |
| ECLASS-15.0 | 27142008 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002298 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

FUSE 10A/32V FK1 - Fuse



2908364

<https://www.phoenixcontact.com/gb/products/2908364>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk