

# UPS-BAT-KIT-WTR 2X12V/13AH - Uninterruptible power supply replacement battery



2908368

<https://www.phoenixcontact.com/gb/products/2908368>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement battery for UPS-BAT/VRLA-WTR... battery modules



## Commercial data

Item number	2908368
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CMUEW3
Product key	CMUEW3
GTIN	4055626297743
Weight per piece (including packing)	11,066 g
Weight per piece (excluding packing)	11,066 g
Customs tariff number	85072080
Country of origin	GB

# UPS-BAT-KIT-WTR 2X12V/13AH - Uninterruptible power supply replacement battery



2908368

<https://www.phoenixcontact.com/gb/products/2908368>

## Technical data

### Notes

#### General

Note on the battery	This product contains a battery with a limited shelf life that must be charged every few months. The product packaging indicates when the battery must be started up or recharged. The general shelf life can be found in the energy storage devices area under "Latest startup".
---------------------	---

### Input data

Input voltage	2x 12 V DC
---------------	------------

### Energy storage

Nominal capacity	13 Ah
Battery module service life	10 Years ... 15 Years (20 °C)
Latest startup date (battery only)	12 Months (0 °C ... 20 °C)
Latest startup (battery only) - range	9 Months ... 12 Months (20 °C ... 30 °C) 6 Months ... 9 Months (30 °C ... 40 °C)
Battery technology	VRLA-WTR
Accumulator type	Genesis G13EPX
IQ technology	no

### Product properties

Product type	Battery
Product family	Replacement battery
Application	for UPS-BAT/VRLA/WTR
IQ technology	no

### Dimensions

Width	167 mm
Height	130 mm
Depth	176 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 60 °C
Max. permissible relative humidity (operation)	≤ 95 %

### Ex data

Suited for EX-applications	no
----------------------------	----

# UPS-BAT-KIT-WTR 2X12V/13AH - Uninterruptible power supply replacement battery



2908368

<https://www.phoenixcontact.com/gb/products/2908368>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2908368>



**GOST-R**

Approval ID: ROSS DE.BL08.D00191

# UPS-BAT-KIT-WTR 2X12V/13AH - Uninterruptible power supply replacement battery



2908368

<https://www.phoenixcontact.com/gb/products/2908368>

## Classifications

### ECLASS

ECLASS-13.0	27059090
ECLASS-15.0	27050492

### ETIM

ETIM 10.0	EC002839
-----------	----------

### UNSPSC

UNSPSC 21.0	26111700
-------------	----------

# UPS-BAT-KIT-WTR 2X12V/13AH - Uninterruptible power supply replacement battery



2908368

<https://www.phoenixcontact.com/gb/products/2908368>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### China RoHS

Environment friendly use period (EFUP)	EFUP-15 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e4ea2098-f56d-4b2f-b9a5-08a1969c5397

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)