

ATP-TB - Partition plate

3046272

<https://www.phoenixcontact.com/gb/products/3046272>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Partition plate, depth: 45.7 mm, width: 3 mm, height: 56 mm, color: dark gray



The figure shows the version in gray

Commercial data

Item number	3046272
Packing unit	50 pc
Minimum order quantity	500 pc
Sales key	BEKZ1X
Product key	BEKZ1X
GTIN	4046356586412
Weight per piece (including packing)	3.69 g
Weight per piece (excluding packing)	3.48 g
Customs tariff number	39269097
Country of origin	DE

ATP-TB - Partition plate



3046272

<https://www.phoenixcontact.com/gb/products/3046272>

Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Dimensions

Width	3 mm
End cover width	1.5 mm
Height	56 mm
Depth	45.7 mm

Material specifications

Color	traffic gray B (RAL 7043)
Flammability rating according to UL 94	V0
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

ATP-TB - Partition plate



3046272

<https://www.phoenixcontact.com/gb/products/3046272>

Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 10.0	EC000886
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ATP-TB - Partition plate



3046272

<https://www.phoenixcontact.com/gb/products/3046272>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk