

# SB-MER 4-8 - Bridge bar

3000589

<https://www.phoenixcontact.com/gb/products/3000589>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bridge bar, pitch: 8.2 mm, number of positions: 4, nominal current: 25 A, length: 25 mm, color: gray/orange

## Commercial data

Item number	3000589
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE1Z2X
Product key	BE1Z2X
GTIN	4046356725552
Weight per piece (including packing)	20.28 g
Weight per piece (excluding packing)	17.04 g
Customs tariff number	85366990
Country of origin	CN

# SB-MER 4-8 - Bridge bar



3000589

<https://www.phoenixcontact.com/gb/products/3000589>

## Technical data

### Product properties

Product type	Bridge bar
Number of positions	4
Pitch	8.2 mm
Potentials	1

### Electrical properties

Maximum load current	25 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

### Connection data

Maximum load current	25 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

### Dimensions

Width	32.8 mm
Height	24.7 mm
Depth	47.42 mm
Length	24.7 mm
Pitch	8.2 mm

### Material specifications

Color	multicolored (RAL -)
	gray (RAL 7042)
	orange (RAL 2003)
Material	Copper
Insulating material	PA

### Mounting

Mounting type	Plug-in mounting
---------------	------------------

# SB-MER 4-8 - Bridge bar



3000589

<https://www.phoenixcontact.com/gb/products/3000589>

## Classifications

### ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

### ETIM

ETIM 10.0	EC000489
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SB-MER 4-8 - Bridge bar



3000589

<https://www.phoenixcontact.com/gb/products/3000589>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)