SCBI 10-8,15 - Screw bridge

3245134

https://www.phoenixcontact.com/gb/products/3245134

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw bridge, with insulating collar, pitch: 8.2 mm, number of positions: 10, nominal current: 24 A, color: silver-colored

Commercial data

Item number	3245134
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE1Z2X
Product key	BE1Z2X
GTIN	4046356574211
Weight per piece (including packing)	22.43 g
Weight per piece (excluding packing)	21.75 g
Customs tariff number	85369095
Country of origin	IN

Technical data

Product properties

Product type	Screw bridge
Number of positions	10
Pitch	8.2 mm

Electrical properties

Maximum load current	24 A

Connection data

Maximum load current	24 A

Dimensions

Pitch	8.2 mm

Material specifications

Color	silver-colored
Material	Copper

Mounting

Mounting type	Screw mounting

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk