

CD 60X60 - Cable duct

3240193

<https://www.phoenixcontact.com/gb/products/3240193>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct for installation and mounting in control cabinets, gray, comprising upper part and mounting base, width: 60 mm, height: 60 mm, length: 2000 mm

Your advantages

- Predetermined breaking point enables tool-free, burr-free removal of bars
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Commercial data

Item number	3240193
Packing unit	18 pc
Minimum order quantity	18 pc
Sales key	BE7431
Product key	BE7431
GTIN	4046356459181
Weight per piece (including packing)	1,105.555 g
Weight per piece (excluding packing)	1,008.6 g
Customs tariff number	39259020
Country of origin	DE

CD 60X60 - Cable duct

3240193

<https://www.phoenixcontact.com/gb/products/3240193>



Technical data

Product properties

Product type	Wiring duct
--------------	-------------

Dimensions

Width	60 mm
Height	60 mm
Length	2000 mm

Material specifications

Color	stone gray (RAL 7030)
Material	PVC
Flammability rating according to UL 94	V0
Components	Lead-free

Cable/line

Halogen-free	no
--------------	----

Mechanical properties

Usage cross-section	3064 mm ² (100 %)
Number of cables at 60% filling volume	94 (2.5 mm ² Ø 3.4 mm)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

CD 60X60 - Cable duct



3240193

<https://www.phoenixcontact.com/gb/products/3240193>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240193>



CSA

Approval ID: 80202282



VDE approval of drawings

Approval ID: 40058456



UL Recognized

Approval ID: E328576

CD 60X60 - Cable duct

3240193

<https://www.phoenixcontact.com/gb/products/3240193>



Classifications

ECLASS

ECLASS-13.0	27400703
ECLASS-15.0	27400703

ETIM

ETIM 10.0	EC000012
-----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

CD 60X60 - Cable duct



3240193

<https://www.phoenixcontact.com/gb/products/3240193>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2.187 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk