

C-BCSI 6/18X4,5 - Cable lug

3240533

<https://www.phoenixcontact.com/gb/products/3240533>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat pin cable lug, yellow, 4 - 6 mm², pin dimensions: 32 x 4.5 mm



Your advantages

- Hard-soldered crimping zone for maximum conductor pull-out forces in connection with CRIMPFOX RCI... pliers
- Easy and reliable conductor entry thanks to 'EASY ENTRY'
- Halogen-free
- Electrogalvanized

Commercial data

Item number	3240533
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BH3461
Product key	BH3461
GTIN	4046356528030
Weight per piece (including packing)	1.923 g
Weight per piece (excluding packing)	1.87 g
Customs tariff number	85369010
Country of origin	CN

C-BCSI 6/18X4,5 - Cable lug

3240533

<https://www.phoenixcontact.com/gb/products/3240533>




Technical data

Product properties

Product type	Connector
Product property	Halogen-free
	With "Easy Entry" system
	Brazed
	PA-insulated

Dimensions

Dimensional drawing	
Width	4.5 mm
Sleeve length	32 mm
Length of the insulating material sleeve	14 mm
Length contact range	18 mm
Maximum stripping length	9 mm
Min. material thickness	1 mm
Inner dimensions of the insulating collar	6.6 mm

Material specifications

Color	yellow (RAL 1018)
Material	Cu
Flammability rating according to UL 94	V2
Coating	electrogalvanized
Insulating material	PA
Components	halogen-free

Mechanical properties

Technical data

Sleeve length	32 mm
---------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
Permanent temperature	105 °C
Short-term temperature	120 °C

C-BCSI 6/18X4,5 - Cable lug


3240533

<https://www.phoenixcontact.com/gb/products/3240533>



Drawings

Dimensional drawing



C-BCSI 6/18X4,5 - Cable lug

3240533

<https://www.phoenixcontact.com/gb/products/3240533>



Classifications

ECLASS

ECLASS-13.0	27400204
ECLASS-15.0	27400204

ETIM

ETIM 10.0	EC001052
-----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

C-BCSI 6/18X4,5 - Cable lug



3240533

<https://www.phoenixcontact.com/gb/products/3240533>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.046 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk