

PTFIX-NS35 - DIN rail adapter



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail adapter, for NS 35 and NS 15 for accommodating 2.5 mm², 4 mm², and 10 mm² FIX blocks in vertical direction, color: gray



Commercial data

Item number	3274054
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	BEAZ11
Product key	BEAZ11
GTIN	4055626377162
Weight per piece (including packing)	4.6 g
Weight per piece (excluding packing)	4.515 g
Customs tariff number	39269097
Country of origin	PL

PTFIX-NS35 - DIN rail adapter



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Technical data

Notes

Assembly note	for NS 35 and NS 15 for accommodating 2.5 mm ² , 4 mm ² , and 10 mm ² FIX blocks in the vertical direction
---------------	---

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	28.6 mm
Height	58.1 mm
Depth	11 mm
Depth on NS 35/7,5	15 mm
Depth on NS 35/15	22.5 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 15

PTFIX-NS35 - DIN rail adapter



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Classifications

ECLASS

ECLASS-13.0	27370419
ECLASS-15.0	27370419

ETIM

ETIM 10.0	EC001024
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PTFIX-NS35 - DIN rail adapter



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.033 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk