# KME - Cable marker carrier

0807083

https://www.phoenixcontact.com/us/products/0807083

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker carrier, white (RAL 9010), unmarked, mounting type: Assembly with cable ties, cable diameter: > 5 mm, text field height: 8 mm, text field width: 20 mm

## Your advantages

- The polyamide conductor and cable marker can be used as a universal marking label for conductor and cable bundles indoors
- Can be labeled with a marker pen, by hand or using a label

## Commercial data

| | |
|---|---|
| Item number | 0807083 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BG12 |
| Product key | BG231A |
| GTIN | 4017918160197 |
| Weight per piece (including packing) | 0.58 g |
| Weight per piece (excluding packing) | 0.5 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Marker carriers |

### Dimensions

| | |
|---|---|
| Width | 27.7 mm |
| Height | 86.5 mm |
| Depth | 5.8 mm |

Text field

| | |
|---|---|
| Text field width | 20 mm |
| Text field height | 8 mm |

### Material specifications

| | |
|---|---|
| Color | white (RAL 9010) |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Relative insulation material temperature index (Elec., UL 746 B) | 125 °C |
| Components | free from silicone and halogen |

### Cable/line

| | |
|---|---|
| External cable diameter | > 5.00 mm |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

### Mounting

| | |
|---|---|
| Mounting type | Assembly with cable ties |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002248 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com