

# US-EML-RS (45,7X45,7) SR - Label



0803826

<https://www.phoenixcontact.com/us/products/0803826>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label, Card, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhesive, Number of individual labels: 4, text field height: 45.7 mm, text field width: 45.7 mm



## Commercial data

Item number	0803826
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2419
GTIN	4055626172552
Weight per piece (including packing)	5.83 g
Weight per piece (excluding packing)	5.83 g
Customs tariff number	39199080
Country of origin	DE

## Technical data

### Product properties

Product type	Device marker
Area of application	Rotary switch Ø 25 mm

### Marking

Number of individual labels	4
Number of individual labels per row	2
Identification technology	Thermotransfer, UV-LED-Technologie

### Dimensions

Width	45.40 mm
Height	45.40 mm
Depth	0.06 mm

### Text field

Text field width	45.7 mm
Text field height	45.7 mm

### Material specifications

Color	silver-colored
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
---------------	---

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# US-EML-RS (45,7X45,7) SR - Label

0803826

<https://www.phoenixcontact.com/us/products/0803826>



## Mounting

Mounting type
adhesive

# US-EML-RS (45,7X45,7) SR - Label



0803826

<https://www.phoenixcontact.com/us/products/0803826>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# US-EML-RS (45,7X45,7) SR - Label



0803826

<https://www.phoenixcontact.com/us/products/0803826>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)