# UM-PRO-KIT-B122-L100-7035 - Housing set

1310984

https://www.phoenixcontact.com/us/products/1310984

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile housing (PA), mounting type: DIN rail mounting, dimensions on the DIN rail: width: 103.8 mm, height: 142.3 mm, depth: 39.45 mm, incl. 2 lateral elements (PA), color: black (9005), for PCBs with width: 122 mm, length: 100 mm, PCB surface: 9840 $mm^2$

## Commercial data

| | |
|---|---|
| Item number | 1310984 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC13 |
| Product key | ACHDAK |
| GTIN | 4063151571269 |
| Weight per piece (including packing) | 125.05 g |
| Weight per piece (excluding packing) | 91.3 g |
| Customs tariff number | 39169010 |
| Country of origin | DE |

## Technical data

### Notes

| | |
|---|---|
| Assembly note | Please observe the assembly instructions available in the download area. |

### Product properties

| | |
|---|---|
| Product type | Stackable housing set |
| Housing type | Profile housing |
| Housing series | UM-PRO |

### Dimensions

| | |
|---|---|
| Width | 103.8 mm |
| Height | 142.3 mm |
| Depth | 39.45 mm |
| Depth from top edge of DIN rail | 32.45 mm |
| Dimensions | 122 mm x 100 mm (PCB dimensions) |

PCB design

| | |
|---|---|
| PCB thickness | 1.4 mm ... 1.8 mm |

### Material specifications

| | |
|---|---|
| Color (Housing side panel) | black (RAL 9005) |
| Color (Housing) | light gray (RAL 7035) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |
| Insulating material | PA |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

### PCB data

| | |
|---|---|
| Number of PCB holders | 3 |
| Type of PCB mount | Insertion/securing with additional elements |
| Total PCB surface | 9840 mm² |
| Thickness of the PCB | 1.4 mm ... 1.8 mm |

### Mounting

| | |
|---|---|
| Mounting type | DIN rail mounting |
| Mounting position | parallel to the DIN rail |

## Packaging specifications

| | |
|---|---|
| Type of packaging | packed in cardboard |
| Outer packaging type | Carton |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1310984

**UL Recognized**
Approval ID: E240868

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27190301 |
| ECLASS-15.0 | 27190301 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001031 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com