

CARRIER-WMT 5 (15X4,2) - Marker carriers



0827283

<https://www.phoenixcontact.com/us/products/0827283>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker carriers, unmarked, cable diameter range: 2.5 ... 5 mm, mounting type: slide-on



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0827283 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BG12 |
| Product key | BG221A |
| GTIN | 4046356435628 |
| Weight per piece (including packing) | 0.361 g |
| Weight per piece (excluding packing) | 0.24 g |
| Customs tariff number | 39269097 |
| Country of origin | SE |

CARRIER-WMT 5 (15X4,2) - Marker carriers



0827283

<https://www.phoenixcontact.com/us/products/0827283>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

Marking

| | |
|-----------|---------|
| Slot type | Profile |
|-----------|---------|

Dimensions

| | |
|--------|-------|
| Width | 7 mm |
| Length | 15 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | transparent |
| Material | PVC |
| Flammability rating according to UL 94 | V0 |
| Components | Free from silicone and cadmium |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 2.5 mm ... 5 mm |
|-------------------------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -30 °C ... 60 °C |
|---------------------------------|------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

CARRIER-WMT 5 (15X4,2) - Marker carriers



0827283

<https://www.phoenixcontact.com/us/products/0827283>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com