

# EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Touch protection, Sheet, unmarked, mounting type: latching, Number of individual labels: 1



## Your advantages

- High level of mechanical and chemical stability
- Suitable for permanent outdoor use
- Stuck or snapped onto labeled CARRIER ... to protect the labeling
- Extremely thick, yet flexible and transparent shock protection

## Commercial data

Item number	0829535
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG18
Product key	BG241B
GTIN	4046356614931
Weight per piece (including packing)	0.193 g
Weight per piece (excluding packing)	0.1 g
Customs tariff number	39204910
Country of origin	DE

# EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

## Technical data

### Product properties

Product type	Cover
Type of packaging	PE bag

### Marking

Number of individual labels	1
-----------------------------	---

### Dimensions

Width	26.90 mm
Height	14.90 mm
Depth	0.30 mm

### Material specifications

RoHS compliant	yes
Foil strength	300 µm
Color	transparent
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

#### Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

#### Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

## Mounting

Mounting type

latching

# EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

## Classifications

### ECLASS

ECLASS-13.0	24292214
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)