

CARRIER-PMP (110X38) - Marker carriers



0831056

<https://www.phoenixcontact.com/us/products/0831056>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker carriers, black (RAL 9005), unmarked, mounting type: screw, rivet, text field height: 38 mm, text field width: 110 mm



Your advantages

- The CARRIER-PMP (110x38) marker carrier is used in conjunction with insertable UC-PMP or PMP-RFID ... labels and PMT and PMST media marking labels.
- The CARRIER features snap-in pins which prevent the labels from falling out. In addition, the PMST (10x38) ... labels can be fixed in the carrier using the RVT-PA 3,5 BK fixing rivet
- They are used to clearly identify devices and control cabinets
- They can be mounted using screws, SCRT ... hose clips or WT cable binders.

Commercial data

Item number	0831056
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG12
Product key	BG261A
GTIN	4046356940870
Weight per piece (including packing)	27.05 g
Weight per piece (excluding packing)	26.92 g
Customs tariff number	39269097
Country of origin	PL

CARRIER-PMP (110X38) - Marker carriers



0831056

<https://www.phoenixcontact.com/us/products/0831056>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	117.50 mm
Height	42.50 mm
Depth	20.00 mm

Text field

Text field width	110 mm
Text field height	38 mm

Material specifications

RoHS compliant	yes
Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Base element material	PA
Relative insulation material temperature index (Elec., UL 746 B)	120 °C
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	screw, rivet
---------------	--------------

CARRIER-PMP (110X38) - Marker carriers



0831056

<https://www.phoenixcontact.com/us/products/0831056>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 10.0	EC002248
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CARRIER-PMP (110X38) - Marker carriers



0831056

<https://www.phoenixcontact.com/us/products/0831056>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.166 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com