

AK-DST/UK - Marker carrier

1000708

<https://www.phoenixcontact.com/us/products/1000708>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker label, for marking groups of terminal blocks with the top marker groove at an angle of 45° e. g. UK terminal blocks, snaps into the marker groove, the marker carrier can be swung over by 120° and is labeled with EST 24 x 4 or ESL 24 x 4.

The figure shows a combination of versions AK-DST-UK marker label and ESL 24 x 4 insert strips

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1000708 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BG12 |
| Product key | BG211A |
| GTIN | 4017918010324 |
| Weight per piece (including packing) | 0.898 g |
| Weight per piece (excluding packing) | 0.896 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

1000708

<https://www.phoenixcontact.com/us/products/1000708>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

Dimensions

| | |
|--------|----------|
| Width | 6.00 mm |
| Height | 39.80 mm |
| Depth | 13.44 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 24 mm |
| Text field height | 4 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | transparent |
| Material | PA/PC |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA/polycarbonate (PC) |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

AK-DST/UK - Marker carrier



1000708

<https://www.phoenixcontact.com/us/products/1000708>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002248 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

AK-DST/UK - Marker carrier



1000708

<https://www.phoenixcontact.com/us/products/1000708>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.009 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com