

# CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising WIREFOX 10, CRIMPFOX DUO 10, AI SORTI BOX RD, AI TWIN SORTI BOX BU, TOOL-KIT STANDARD EMPTY

## Product description

Tool set, equipped

## Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools
- Universal tools sets with WIREFOX 10, CRIMPFOX-DUO tools from TOOL fox
- Ideal for TWIN ferrule
- Rugged and heavy-duty tool bags

## Commercial data

Item number	1044971
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4055626622859
Weight per piece (including packing)	1,056.1 g
Weight per piece (excluding packing)	1,056.1 g
Customs tariff number	82060000
Country of origin	SE

# CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

## Set consists of

### CRIMPFOX DUO 10 - Crimping pliers

1031721

<https://www.phoenixcontact.com/us/products/1031721>



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F, min. cross section: 0.14 mm<sup>2</sup>, max. cross section: 10 mm<sup>2</sup>, for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, rotating die, lateral and frontal insertion, compression: Trapezoidal crimp, weight 305 g, black/green

---

### WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

# CRIMPFOX DUO 10 SET - Tool set

1044971

<https://www.phoenixcontact.com/us/products/1044971>

## AI SORTI BOX RD - Assortment box

3202960

<https://www.phoenixcontact.com/us/products/3202960>



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

---

## AI-TWIN SORTI BOX BU - Assortment box

3202986

<https://www.phoenixcontact.com/us/products/3202986>



**Assortment box**, supplied with TWIN ferrules in accordance with DIN 46228-4, 50 pcs. each AI-TWIN 2x0,5-8 WH, AI-TWIN 2x0,75-8 GY, AI-TWIN 2x1-8 RD, AI-TWIN 2x1,5-8 BK, 25 pcs. AI-TWIN 2x2,5-10 BU

# CRIMPFOX DUO 10 SET - Tool set

1044971

<https://www.phoenixcontact.com/us/products/1044971>



## TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

<https://www.phoenixcontact.com/us/products/1212423>



Tool box, unequipped

# CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Tool set

Type of packaging

Bag

Compression

Trapezoidal crimp

### Electrical properties

Fuse

DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F

### Dimensions

Width

65 mm

Height

315 mm

Length

165 mm

### Material specifications

Color

black (RAL 9005)

# CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

## Classifications

### ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

### ETIM

ETIM 10.0	EC000149
-----------	----------

### UNSPSC

UNSPSC 21.0	27113200
-------------	----------

# CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)