

# ZB 5/OG,LGS: 10-100 - Zack marker strip

1050211

<https://www.phoenixcontact.com/us/products/1050211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, orange (RAL 2003), labeled, printed horizontally: Sets of ten 10 - 100, mounting type: snap into tall marker groove, for terminal block width: 5.2 mm, Number of individual labels: 10

## Commercial data

Item number	1050211
Packing unit	1 pc
Sales key	BG05
Product key	BG2122
GTIN	4017918015633
Weight per piece (including packing)	1.04 g
Weight per piece (excluding packing)	1.04 g
Customs tariff number	49119900
Country of origin	PL

# ZB 5/OG,LGS: 10-100 - Zack marker strip



1050211

<https://www.phoenixcontact.com/us/products/1050211>

## Technical data

### Product properties

Product type	Terminal marker
Pitch	5.2 mm

### Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Printing direction	printed horizontally
Printing	Sets of ten 10 - 100
Slot type	high

### Dimensions

Width	4.60 mm
Height	10.50 mm
Depth	4.30 mm
Pitch	5.2 mm

### Material specifications

Color	orange (RAL 2003)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN VDE 0611

### Mounting

Mounting type	snap into tall marker groove
---------------	------------------------------

# ZB 5/OG,LGS: 10-100 - Zack marker strip



1050211

<https://www.phoenixcontact.com/us/products/1050211>

## Classifications

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# ZB 5/OG,LGS: 10-100 - Zack marker strip



1050211

<https://www.phoenixcontact.com/us/products/1050211>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)