

# FT NUT M25 GN - Nut

1049830

<https://www.phoenixcontact.com/us/products/1049830>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Nut, Range of articles: PRC 35, color: green



## Product description

Nut for color-coding device interfaces

## Your advantages

- Color coding for PRC connectors
- Easy installation
- Other colors available on request

## Commercial data

Item number	1049830
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB03
Product key	ABL CZB
GTIN	4055626661575
Weight per piece (including packing)	3.17 g
Weight per piece (excluding packing)	2.735 g
Customs tariff number	39269097
Country of origin	PL

# FT NUT M25 GN - Nut

1049830

<https://www.phoenixcontact.com/us/products/1049830>



## Technical data


### Product properties

Product type	Panel feed-through
Product family	PRC 35

### Insulation characteristics

Degree of pollution	2
---------------------	---

### Dimensions

Dimensional drawing	
Width	6.5 mm
Height	38.4 mm
Length	34 mm
Wrench size, union nut	34 mm

### Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94	V0
Material for screw connection	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-20 °C ... 65 °C
Ambient temperature (assembly)	-5 °C ... 85 °C

# FT NUT M25 GN - Nut


1049830

<https://www.phoenixcontact.com/us/products/1049830>



## Drawings

Dimensional drawing



# FT NUT M25 GN - Nut



1049830

<https://www.phoenixcontact.com/us/products/1049830>

## Classifications

### ECLASS

ECLASS-13.0	27440691
ECLASS-15.0	27140807

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FT NUT M25 GN - Nut



1049830

<https://www.phoenixcontact.com/us/products/1049830>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.031 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)