

# RTU READY EX UPS 161408 - Control cabinet



1100665

<https://www.phoenixcontact.com/us/products/1100665>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Prewired control cabinet with power supply, battery backup, surge protective device, and circuit breaker for use with remote control and monitoring devices



RTU READY... 181610 version shown

## Product description

To simplify the selection and installation of wireless devices, Phoenix Contact offers the RTU READY... enclosure system to house radios, PLCs, or other control products. The prewired control cabinet provides a 24 V DC power supply and surge protection for line power and antenna connections, and terminal blocks for easy connectivity, all mounted on standard NS 35 mounting rail.

The selected components provide a robust housing with reliable power. Simply add a radio, antenna, or controller to complete the system.

## Your advantages

- UPS with 24 V DC backup battery
- 100 V AC ... 240 V AC nominal input voltage range
- Supply voltage: 24 V DC
- Prewired cabinetry with extra terminal blocks for simple, flexible installation
- UL 508A Listed
- COAXTRAB surge protection for antenna connection
- Class I, Div. 2 components

## Commercial data

Item number	1100665
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DT02
Product key	DTHDCA
GTIN	4063151030735
Weight per piece (including packing)	10,668 g
Weight per piece (excluding packing)	10,160 g
Country of origin	US

# RTU READY EX UPS 161408 - Control cabinet



1100665

<https://www.phoenixcontact.com/us/products/1100665>

## Set consists of

### MINI-DC-UPS/24DC/2 - Uninterruptible power supply

2866640

<https://www.phoenixcontact.com/us/products/2866640>



Uninterruptible power supply with integrated power supply unit, 2 A, in combination with MINI-BAT/24/DC 0.8 AH or 1.3 AH

---

### MINI-BAT/24DC/0.8AH - Battery module

2866666

<https://www.phoenixcontact.com/us/products/2866666>



Battery module (device with battery), lead AGM, VRLA technology, 24 V DC, 0.8 Ah.

1100665

<https://www.phoenixcontact.com/us/products/1100665>

## Technical data

### Product properties

Product type	Control box
--------------	-------------

### Electrical properties

#### Supply

Supply voltage range	85 V AC ... 264 V AC
Typical current consumption	2 A

### Dimensions

Width	384 mm
Height	443 mm
Depth	221 mm

### Material specifications

Housing material	PC
------------------	----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	0 °C ... 40 °C
---------------------------------	----------------

### Standards and regulations

#### Standards

Standards/regulations	UL 508A
-----------------------	---------

# RTU READY EX UPS 161408 - Control cabinet



1100665

<https://www.phoenixcontact.com/us/products/1100665>

## Classifications

### ECLASS

ECLASS-13.0	27370190
-------------	----------

# RTU READY EX UPS 161408 - Control cabinet



1100665

<https://www.phoenixcontact.com/us/products/1100665>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
-----------------------------------------	-------------------------------------------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)