

# SF-SOCKET SET 47 - Tool set



1200292

<https://www.phoenixcontact.com/us/products/1200292>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**1/4" socket set**, 47-piece, 1/4" reversible ratchet, 48 teeth with fast locking system, 50 mm and 100 mm 1/4" extensions, 1/4" screwdriver handle, 150 mm 1/4" flexible extension, 1/4" Cardan joint, 1/4" T-handle  
2 x 1/4" bit adapter, 13 knurled 1/4" sockets, wrench size: 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, 21 knurled socket bits: 6 x Torx® T10, T15, T20, T25, T30, T40, 6 x Hex 3, 4, 5, 6, 7, 8 mm, 3 x Phillips recess® PH1, PH2, PH3, 3 x Pozidriv® PZ1, PZ2, PZ3, 3 x slotted 4, 5.5, 7 mm, Allen wrench Hex 1.27, 1.5, 2, 2.5 mm, breakage and impact-resistant plastic case with metal fastening

## Your advantages

- Robust cases for safe storage
- Ratcheting mechanism with 48 teeth enables precise working, even in tight working environments
- Made from chrome vanadium steel for a long service life
- Solid 1/4" screw set with comprehensive equipment
- Optimum power transmission without damaging the screw head, thanks to special edge geometries

## Commercial data

Item number	1200292
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH314G
GTIN	4055626388113
Weight per piece (including packing)	1,603.4 g
Weight per piece (excluding packing)	1,603.4 g
Customs tariff number	82060000
Country of origin	TW

# SF-SOCKET SET 47 - Tool set



1200292

<https://www.phoenixcontact.com/us/products/1200292>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Tool set

Type of packaging

Case

# SF-SOCKET SET 47 - Tool set



1200292

<https://www.phoenixcontact.com/us/products/1200292>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1200292>



**EAC**

Approval ID: RU C-DE.AI30.B.01750

# SF-SOCKET SET 47 - Tool set



1200292

<https://www.phoenixcontact.com/us/products/1200292>

## Classifications

### ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

### ETIM

ETIM 10.0	EC000149
-----------	----------

### UNSPSC

UNSPSC 21.0	27113200
-------------	----------

# SF-SOCKET SET 47 - Tool set



1200292

<https://www.phoenixcontact.com/us/products/1200292>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	20.142 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)