CES-B24-SFC-M-15,6 - Locking element

1423745

https://www.phoenixcontact.com/us/products/1423745

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Locking element, design: B24, material: Steel, galvanized, length: 146 mm, width: 57 mm, height: 15.6 mm

Commercial data

Item number	1423745
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF67
Product key	AF7CZX
GTIN	4055626353432
Weight per piece (including packing)	107.33 g
Weight per piece (excluding packing)	100 g
Customs tariff number	73269098
Country of origin	DE

Technical data

Product properties

Product type	Cover plate
Type	B24

Dimensions

Dimensional drawing	
Width	57 mm
Height	15.6 mm
Length	146 mm

Material specifications

Material	Steel, galvanized

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C

Mounting

Assembly note	suitable for article 0801647, V/C: 01 (version batch), see printing of the packaging label

Drawings

Dimensional drawing



Dimensional drawing

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1423745

DNV
Approval ID: TAE00003VJ

Classifications

ECLASS

ECLASS-13.0	27440192
ECLASS-15.0	27440192

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com