

WIREFOX 16 - Stripping tool



1212155

<https://www.phoenixcontact.com/us/products/1212155>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping tool, for cables and conductors from 4 - 16 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

Product description

Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212152 WIREFOX 10/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212153 WIREFOX 16/SB

Your advantages

- Flexible, adjustable limit stop for the stripping length
- Practical integrated wire cutter
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212155 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3121 |
| GTIN | 4046356454414 |
| Weight per piece (including packing) | 210.3 g |
| Weight per piece (excluding packing) | 212.7 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

WIREFOX 16 - Stripping tool



1212155

<https://www.phoenixcontact.com/us/products/1212155>

Technical data

Notes

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Product properties

| | |
|------------------|--|
| Product type | Stripping tool |
| Application | Standard |
| Product property | Automatic adjustment mechanism |
| | Replaceable stripping blade |
| | Length stop for setting the stripping length |
| | Integrated wire cutter |

Connection data

Conductor connection

| | |
|-----------------------------|--|
| Cross section range, metric | 4 mm ² ... 16 mm ² (Stripping range) |
| | 1.5 mm ² (Cutting zone) |
| Cross section range AWG | 12 ... 5 (Stripping range) |
| | 16 (Cutting zone) |
| Stripping length | 2 mm ... 18 mm |

Dimensions

| | |
|--------|--------|
| Width | 20 mm |
| Height | 90 mm |
| Length | 191 mm |

Material specifications

| | |
|-------|-------------|
| Color | black/green |
|-------|-------------|

WIREFOX 16 - Stripping tool

1212155

<https://www.phoenixcontact.com/us/products/1212155>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212155>



EAC

Approval ID: RU x-DE.xx08.B.02974

WIREFOX 16 - Stripping tool



1212155

<https://www.phoenixcontact.com/us/products/1212155>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043706 |
| ECLASS-15.0 | 21043706 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002109 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

WIREFOX 16 - Stripping tool



1212155

<https://www.phoenixcontact.com/us/products/1212155>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com