

# CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for non-insulated cable lugs, 4 ... 10 mm<sup>2</sup>, double indent crimp

## Your advantages

- The CRIMPFOX-RC 10 completes the range of crimping pliers for uninsulated cable lugs and insulated tube lugs
- All pliers of this design reduce the amount of force required for crimping by 25%

## Commercial data

Item number	1212061
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3133
GTIN	4046356453936
Weight per piece (including packing)	660.205 g
Weight per piece (excluding packing)	660.2 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Product type	Crimping tool
Compression	Indent crimp
Product property	Indent crimp
	Up to 25% lower actuation force

#### Crimping position 1

Max. cross section	4 mm <sup>2</sup>
AWG max	12

#### Crimping position 2

Max. cross section	6 mm <sup>2</sup>
AWG max	10

#### Crimping position 3

Max. cross section	10 mm <sup>2</sup>
AWG max	8

### Connection data

#### Conductor connection

Cross section range, metric	4 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Cross section range AWG	12 ... 8

### Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212061>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)