

# WIREFOX SAC - Stripping tool



1212623

<https://www.phoenixcontact.com/us/products/1212623>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 4.4 to 7 mm, any stripping length

## Your advantages

- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212623       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3121        |
| GTIN                                 | 4046356634625 |
| Weight per piece (including packing) | 150.2 g       |
| Weight per piece (excluding packing) | 142 g         |
| Customs tariff number                | 82032000      |
| Country of origin                    | DE            |

# WIREFOX SAC - Stripping tool



1212623

<https://www.phoenixcontact.com/us/products/1212623>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                  |                                |
|------------------|--------------------------------|
| Product type     | Stripping tool                 |
| Application      | Standard                       |
|                  | PUR                            |
|                  | TPE                            |
| Product property | Automatic adjustment mechanism |
|                  | Replaceable stripping blade    |
|                  | Any stripping length           |

### Dimensions

|                     |                 |
|---------------------|-----------------|
| Length              | 165 mm          |
| External dimensions |                 |
| Outside diameter    | 4.4 mm ... 7 mm |

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

### Cable/line

|                         |                 |
|-------------------------|-----------------|
| External cable diameter | 4.4 mm ... 7 mm |
|-------------------------|-----------------|

# WIREFOX SAC - Stripping tool


1212623

<https://www.phoenixcontact.com/us/products/1212623>



## Drawings

Schematic diagram



# WIREFOX SAC - Stripping tool



1212623

<https://www.phoenixcontact.com/us/products/1212623>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212623>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# WIREFOX SAC - Stripping tool



1212623

<https://www.phoenixcontact.com/us/products/1212623>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043706 |
| ECLASS-15.0 | 21043706 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002109 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# WIREFOX SAC - Stripping tool



1212623

<https://www.phoenixcontact.com/us/products/1212623>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)