VS-08-SD-F - Protective cover

1652606

https://www.phoenixcontact.com/us/products/1652606

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cover, IP67, flat design, to cover the contact insert in the panel mounting frame, color: gray



Commercial data

Item number	1652606
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNNDZ
GTIN	4017918953034
Weight per piece (including packing)	3.6 g
Weight per piece (excluding packing)	2.857 g
Customs tariff number	39235090
Country of origin	DE

Technical data

Product properties

Product type	Protective cover
Connection profile	RJ45

Dimensions

Width	22 mm
Height	10 mm
Length	55 mm

Material specifications

Color	gray
Material	Plastic
Flammability rating according to UL 94	V0
Seal material	EDPM, self-greasing
Seal material, O-ring	EDPM, self-greasing
Housing material	PA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

Classifications

ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

ETIM

ETIM 10.0	EC002314

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.048 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com